

## Features for the ARP20, 30 and 40 series

Expanded lineup: 3 types of set pressure and the body size allow more freedom in designing a circuit.

(1) Body sizes: 3 sizes (ARP20, 30 and 40)

The existing ARP3000 series: Only 1 size is available.

(2) Pressure range: 3 different pressures (0.2, 0.4 and 0.6MPa)

ARP3000 series: Only 0.3MPa is available.

(3) Sensitivity: within 0.2%F.S.

ARP3000 series: Within approximately 0.3%F.S.

(4) Air consumption: Air consumption of the new model is reduced to 80% of the existing one.  
(as compared with ARP3000 series when 0.3MPa pressure is applied.)

(5) The new model is equipped with reverse flow function. (ARP20K, 30K and 40K)

(6) A digital pressure switch is available for the new model.