




ORIGINAL INSTRUCTIONS

Instruction Manual

Lock-Up Valve

Series IL201/211/220



The intended use of these Lock-Up Valves is to control the air in the secondary pressurized air system. Depending on the signal pressure the types 201 and 211 are locking the air and the type 220 is relieving the air. Validated according to ISO 13849.

1 Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)^{*)}, and other safety regulations.

^{*)} ISO 4414: Pneumatic fluid power - - General rules relating to systems.
ISO 4413: Hydraulic fluid power - - General rules relating to systems.

- IEC 60204-1: Safety of machinery - -Electrical equipment of machines. (Part 1: General requirements)
- ISO 10218-1: Manipulating industrial robots -Safety.etc.

This manual contains essential information for the protection of users and others from possible injury and/or equipment damage.

- Read this manual before using the product, to ensure correct handling, and read the manuals of related apparatus before use.
- Keep this manual in a safe place for future reference.
- To ensure safety of personnel and equipment the safety instructions in this manual must be observed, along with other relevant safety practices.

| | | |
|--|----------------|--|
| | Caution | Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury. |
| | Warning | Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury. |
| | Danger | Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury. |

Warning

- The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.**
- Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalogue information,

1 Safety Instructions - continued

with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

- Only personnel with appropriate training should operate machinery and equipment.**

The product specified here may become unsafe if handled incorrectly.

The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

- Do not service or attempt to remove product and machinery/equipment until safety is confirmed.**

1) The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.

2) When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.

3) Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.

- Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions.**

1) Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.

2) Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustions and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specification described in the product catalogue.

3) An application which could have negative effects on people, property or animals requiring special safety analysis outside the scope of ISO 13849 described in this document.

4) Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function,

and periodical checks to confirm proper operation.

- Always ensure compliance with relevant safety laws and standards.**

- All electrical work must be carried out in a safe manner by a qualified person in compliance with applicable national regulations.

Caution

The product is provided for use in manufacturing industries.

The product herein described is basically provided for peaceful use in manufacturing industries.

If considering using the product in other industries, consult SMC beforehand and exchange specifications or a contract if necessary.

If anything is unclear, contact your nearest sales branch.

2 Specifications

2.1 Standard Specifications

| Model | IL201 | IL211 | IL220 |
|-------------------------------------|------------------------------------|---------------|--------|
| Action | Single action | Double acting | 3 port |
| Signal pressure | Max.1.0 MPa ^{Note 1)} | | |
| Set pressure range | 0.14 to 0.7 MPa ^{Note 1)} | | |
| Shut-off pneumatic circuit pressure | Max.0.7 MPa | | |
| Ambient and fluid temperature | -5 to +60 °C | | |
| Port size | Rc1/4 | | |
| Differential | 0.01 MPa ^{Note 2)} | | |
| Type of fluid | Air | | |
| Fluid quality | Oil-free filtered to 5µm air | | |
| Min. operating frequency | 1 cycle / 30 days | | |
| Flow rate Cv | 0.9 | 0.9 | 1.1 |

2 Specifications - continued

| Standards | Complies with the basic and well-tried safety principles of ISO 13849-2:2012 | | |
|------------------|--|---------|--------|
| B ₁₀ | 8,000 cycle ^{Note 3)} | | |
| B _{10d} | 16,000 cycle ^{Note 3)} | | |
| Weight | 0.45 kg | 0.64 kg | 0.7 kg |

Table 1

Notes:

Note 1) Provide a differential pressure of 0.1 MPa or more between the signal pressure and set pressure.

If the differential pressure is small, the internal part is worn out due to the structure of this product and the bleed amount from the exhaust port increases, which may affect the characteristics.

Note 2) Pressure difference between lock activated and lock released.

Note 3) Under SMC test conditions. The B₁₀ figure is estimated from SMC life tests. The B_{10d} figure is derived from B₁₀ using the assumption in EN ISO 13849-1:2008 Annex C. Contact SMC for details.

2.2 Principle of Operation

The signal air pressure enters the upper diaphragm chamber (1) to generate a force. When this force is larger than the force generated by compressing the adjusting spring (3), the upper diaphragm (2) is pushed up, the exhaust port (4) is closed, and the signal air pressure enters the lower diaphragm chamber (5) and acts the lower diaphragm (6). This pushes down the piston (7) to open the valve. IL201 and IL211 enter the status, in which the flow path between IN and OUT is opened. IL220 enters the status, in which the flow path between IN1 and OUT is opened. If the signal air pressure drops to a level below the set pressure for some reason, the upper diaphragm (2) is pushed down, the pressure inside the lower diaphragm (6) is exhausted from the exhaust port (4), and the valve (8) is closed by the force of the spring (9). At this time, IN and OUT are shut down in IL201 and IL211. In IL220, IN1 and OUT are shut down, and the flow path between IN2 and OUT is opened. The set pressure is adjusted with the adjusting screw (10).




Figure 1




Figure 2

2 Specifications - continued




Figure 3

Caution

Special products might have specifications different from those shown in this section. Contact SMC for specific drawings. These drawings will give the appropriate specification details and compliance with the safety principles of ISO 13849, if applicable.

3 Installation

3.1 Installation

Warning

- Do not install the product unless the safety instructions have been read and understood.

3.2 Environment

Warning

- Do not use in an environment where corrosive gases, chemicals, salt water or steam are present.
- Do not use in an explosive atmosphere.
- Do not expose to direct sunlight. Use a suitable protective cover.
- Do not install in a location subject to vibration or impact. Check the product specifications.
- Do not mount in a location exposed to radiant heat.

3.3 Piping

Caution

- Before piping make sure to clean up chips, cutting oil, dust etc.
- When installing piping or fittings, ensure sealant material does not enter inside the port. When using seal tape, leave 1.5 to 2 threads exposed on the end of the pipe/fitting.
- Tighten fittings to the specified tightening torque.

3 Installation – continued

3.4 Lubrication

Caution


- SMC products have been lubricated for life at manufacture, and do not require lubrication in service.
- If a lubricant is used in the system, use turbine oil Class 1 (no additive), ISO VG32. Once lubricant is used in the system, lubrication must be continued because the original lubricant applied during manufacturing will be washed away.

4 Settings

Warning


Since connected equipment will operate when the manual override is activated, confirm that conditions are safe prior to activation.

5 How to Order




6 Outline Dimensions (mm)

6.1 IL201




6 Outline Dimensions (mm) - continued

6.2 IL211



6 Outline Dimensions (mm) - continued

6.3 IL220



7 Maintenance

7.1 General Maintenance

Caution

- Not following proper maintenance procedures could cause the product to malfunction and lead to equipment damage.
- If handled improperly, compressed air can be dangerous. Maintenance of pneumatic systems should be performed only by qualified personnel.
- Before performing maintenance, turn off the power supply and be sure to

cut off the supply pressure. Confirm that the air is released to atmosphere.

- After installation and maintenance, apply operating pressure and power to the equipment and perform appropriate functional and leakage tests to make sure the equipment is installed correctly.
- If any electrical connections are disturbed during maintenance, ensure they are reconnected correctly and safety checks are carried out as required to ensure continued compliance with applicable national regulations.
- Do not make any modification to the product.
- Do not disassemble the product, unless required by installation or maintenance instructions.

8 Limitations of Use

8.1 Limited warranty and Disclaimer/Compliance Requirements

• The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements". Read and accept them before using the product.

Limited warranty and Disclaimer

- 1) The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first⁽¹⁾. Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- 2) For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3) Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalogue for the particular products.

8 Limitations of Use - continued

⁽¹⁾ Vacuum pads are excluded from this 1 year warranty. A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements

- 1) The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- 2) The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

Caution

- SMC products are not intended for use as instruments for legal metrology. Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country. Therefore, SMC products cannot be used for business or certification ordained by the metrology (measurement) laws of each country.

Warning

- Any use in an ISO 13849 system must be within the specified limit and application condition. The user is responsible for the specification, design, implementation, validation and maintenance of the safety system(SRP/CS)

9 Contacts

| | |
|-------------------|--|
| AUSTRIA | SMC Pneumatik GmbH, Girakstrasse 8, AT-2100 Korneuburg, Austria |
| BELGIUM | SMC Pneumatics N.V./S.A. Nijverheidsstraat 20, B-2160 Wommelgem, Belgium |
| BULGARIA | SMC Industrial Automation Bulgaria EOOD, Business Park Sofia, Building 8-6th floor, BG-1715 Sofia, Bulgaria |
| CROATIA | SMC IndustrijskaAutomatikad.o.o. ZagrebačkaAvenija 104,10 000 Zagreb |
| CZECH REP. | SMC Industrial Automation CZ s.r.o. Hudcova 78a, CZ-61200 Brno, Czech Republic |
| DENMARK | SMC Pneumatik A/S, Egeskovvej 1, DK-8700 Horsens, Denmark |
| ESTONIA | SMC Pneumatics Estonia Oü, Laki 12, EE-10621 Tallinn, Estonia |
| FINLAND | SMC Pneumatics Finland Oy, PL72, Tiistinniityntie 4, SF-02031 Espoo, Finland |
| FRANCE | SMC Pneumatique SA.1, Boulevard de Strasbourg, Parc Gustave Eiffel, Bussy Saint Georges, F-77607 Marne La Vallée Cedex 3, France |
| GERMANY | SMC Pneumatik GmbH, Boschring 13-15, 63329 Egelsbach, Germany |
| GREECE | SMC Italia Hellas Branch, Anagenniseos 7-9-P.C. 14342 N.Philadelphia, Athens, Greece |
| HUNGARY | SMC Hungary IpariAutomatizálásiKft. Torbágy u. 19, HU-2045 Törökbálint, Hungary |
| IRELAND | SMC Pneumatics (Ireland) Ltd. 2002 Citywest Business Campus, Naas Road, Saggart, Co. Dublin, Ireland |
| ITALY | SMC Italia S.p.A. Via Garibaldi 62, I-20061 Carugate, (Milano), Italy |

| | |
|--------------------|--|
| LATVIA | SMC Pneumatics Latvia SIA, Dzelzavas str. 120g, Riga, LV-1021, Latvia |
| LITHUANIA | UAB "SMC Pneumatics", Oslo g. 1, LT-04123 Vilnius, Lithuania |
| NETHERLANDS | SMC Pneumatics B.V. De Ruyterkade 120, NL-1011 AB Amsterdam, the Netherlands |
| NORWAY | SMC Pneumatics Norway AS, Vollsveien 13 C, GranfosNæringspark, N-1366 Lysaker, Norway |
| POLAND | SMC Industrial Automation, Polska Sp z o.o. 02-826 Warszawa, ul. Poloneza 89 |
| PORTUGAL | SMC España S.A. Zuazobidea 14, 01015 Vitoria, Spain |
| ROMANIA | SMC Romania S.r.l. StrFrunzei 29, Sector 2, Bucharest, Romania |
| RUSSIA | SMC Pneumatik LLC. Business centre, building 3, 15 Kondratjevskij prospect, St.Petersburg, Russia, 195197 |
| SLOVAKIA | SMC PriemyselnáAutomatizáciaSpols.r.o. Fantranská 1223, Teplickánadvahom, 01301, Slovakia |
| SLOVENIA | SMC IndustrijskaAvtomatikad.o.o. Mirskacesta 7, SLO-8210 Trebnje, Slovenia |
| SPAIN | SMC España S.A. Zuazobidea 14, 01015 Vitoria, Spain |
| SWEDEN | SMC Pneumatics Sweden AB, Ekhagsvägen 29-31, SE-141 71 Segeltorp, Sweden |
| SWITZERLAND | SMC Pneumatik AG, Dorfstrasse 7, Postfach, 8484 Weissingen, Switzerland |
| TURKEY | SMC PnömatikSanayiTicaretveServis A.Ş. GülbaharCaddesi, Aydın Plaza, No: 9/4 Güneşli – 34212, Istanbul |
| UK | SMC Pneumatics (U.K.) Ltd. Vincent Avenue, Crownhill, Milton Keynes, Buckinghamshire MK8 0AN, United Kingdom |

SMC Corporation

URL : [http:// www.smcworld.com](http://www.smcworld.com) (Global) [http:// www.smceu.com](http://www.smceu.com) (Europe)
 'SMC Corporation, Akihabara UDX15F, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101 0021

Specifications are subject to change without prior notice from the manufacturer.

© 2016 SMC Corporation All Rights Reserved.

Template DKP50047-F-085D